


Typical Dome

Flex-C Trac to Flex-C Trac Splice

For Ribs and Tension Ring as Needed



Flex-C Trac shown without strap to facilitate viewing.

Securing Methods:

The shape of 3 5/8" and 6", 20 gauge Flex-C Trac can be secured by either flattening the Hammer-Lock tabs or inserting screws through the flanges of each link on both sides of the track. For 3 5/8" and 6", 18 and 16 gauge Flex-C Trac and 16 gauge Flex-C Angle, the shape must be secured by inserting screws through the flanges of each link on both sides of the track.

FLEX-ABILITY
CONCEPTS

Distributor:
Contractor:
Project:
Product Detail: DD8

Quantity:
Approved By:
Architect:
Date:

5500 W. Reno, Suite 300
Oklahoma City, OK 73127
Tel: 405-996-5343 Fax: 405-996-5353
E-mail: info@flexabilityconcepts.com
Web: www.flexabilityconcepts.com